




























Phonak Sky™ platform comparison.

Features		Lumity 90	Marvel 90
Phonak SmartSpeech™ Technology	 AutoSense Sky OS	5.0	3.0
	 StereoZoom 2.0	Yes	-
	 SpeechSensor	Yes	-
	 Speech Enhancer	Yes	-
	 Dynamic Noise Cancellation	Yes	-
	 Motion Sensor Hearing	Yes	-
Additional features	 UltraZoom	Yes	Yes
	 WindBlock	Yes	Yes
	 Detailed wearing time*	Yes	-
	 Feedback overtuning	Yes	-
	 Connection alerts Off: 0 – 3 yrs, On: Older age groups	Yes	-
	 QuickSync uncoupling	Yes	-
	Adaptive compression speeds and Loud input knee point	Yes	-
Connectivity	 Active Bluetooth® connections / Bluetooth® pairings	2 connections 8 pairings	1 connection 2 pairings
	 Hands-free calls	Improved	Yes
	 Tap Control*	Yes	-
	 myPhonak Junior	Yes	Yes
	 RogerDirect™ (+ hearing aid mic setting)	Yes	Yes
	 CROS-R compatible*	Yes	-















*Rechargeable Sky L-PR only

Phonak Sky™ platform comparison.


Features		Lumity 70	Marvel 70
	 AutoSense Sky OS	5.0	3.0
Phonak SmartSpeech™ Technology	 StereoZoom 2.0	Manual program	-
	 Dynamic Noise Cancellation	Yes	-
	 Motion Sensor Hearing	Yes	-
	 UltraZoom	Yes	Yes
Additional features	 WindBlock	Yes	Yes
	 Detailed wearing time*	Yes	-
	 Feedback overtuning	Yes	-
	 Connection alerts Off: 0 – 3 yrs, On: Older age groups	Yes	-
	 QuickSync uncoupling	Yes	-
	Adaptive compression speeds and Loud input knee point	Yes	-
	 Active Bluetooth® connections	2	1
Connectivity	 Bluetooth® pairings	8	2
	 Hands-free calls	Improved	Yes
	 Tap Control*	Yes	-
	 myPhonak Junior	Yes	Yes
	 RogerDirect™ (+ hearing aid mic setting)	Yes	Yes
	 CROS-R compatible*	Yes	-

*Rechargeable Sky L-PR only

Phonak Sky™ platform comparison.

Features		Lumity 50	Marvel 50
Feature comparison	 AutoSense Sky OS	5.0	3.0
	 Motion Sensor Hearing*	Yes	-
	 UltraZoom	Yes	Yes
	 WindBlock		
	- Calm situation	WindBlock weak	-
	- Speech in Noise	NoiseBlock + WindBlock weak	NoiseBlock
	- Comfort in Noise	NoiseBlock + WindBlock weak	NoiseBlock
	 Detailed wearing time*	Yes	-
	 Feedback overtuning	Yes	-
	 Connection alerts Off: 0 – 3 yrs, On: Older age groups	Yes	-
	 QuickSync uncoupling	Yes	-
	Adaptive compression speeds and Loud input knee point	Yes	-
	Microphone directionality – Calm situation	RES	RES
	Connectivity	 Active Bluetooth® connections	2
 Bluetooth® pairings		8	2
 Hands-free calls		Improved	Yes
 myPhonak Junior		Yes	Yes
 RogerDirect™ (+ hearing aid mic setting)		Omni, RES, Fixed	Omni, RES, Fixed
 CROS-R compatible*		Yes	-

*Rechargeable Sky L-PR only



life is on

Since 1947, Phonak is dedicated to preserving life quality by opening new acoustic worlds. Already back then, in the days of our foundation, our company was driven by a formative conviction: We believe that well-hearing equates to well-being and thus is essential for living life to the fullest. In fact, the sense of hearing is directly linked to social, emotional, cognitive and physical well-being. Today as in future, we thrive to offer the broadest portfolio of innovative hearing solutions. And, together with our hearing care professionals, we keep on focusing on what matters most: improving speech understanding, changing people's lives and having a positive effect on society as a whole.

www.phonak.com