

Phonak Virto™ 1

Phonak Virto I-R (I90/I70/I50/I30)

Technical Data




M Receiver


2 cm³ coupler data

ANSI / ASA S3.22-2014 (R2020)
IEC 60118-0:2022

Output sound pressure level



Acoustic gain



Frequency range	<100 Hz – 7000 Hz			
Total harmonic distortion	500 Hz	800 Hz	1600 Hz	3200 Hz
	1.0%	1.5%	1.0%	1.0%
Expected operating time*	24 h			
Equivalent input noise level	19 dBSPL			

General test information

- Specific measurement settings are used. RTS adjustment with volume control.
- The device is operating in linear mode.
- Low-level expansion is active.
- Unless otherwise specified, all data obtained are measured with 5 mm tubing and Phonak Target measurement settings.
- The latency of the audio signal determined according to an internal standard is 6.2 ms.

Warnings

- ⚠ Changes or modifications to the hearing aid that are not explicitly approved by the manufacturer are not permitted. Such changes may damage the ear or the hearing aid.


* Expected operating time of the rechargeable battery depends on active features, the use of wireless accessories, hearing loss, battery age and sound environment.

P Receiver


2 cm³ coupler data

ANSI / ASA S3.22-2014 (R2020)
IEC 60118-0:2022

Output sound pressure level



Acoustic gain



Frequency range	<100 Hz – 6700 Hz			
Total harmonic distortion	500 Hz	800 Hz	1600 Hz	3200 Hz
	1.0%	1.0%	1.0%	1.0%
Expected operating time*	24 h			
Equivalent input noise level	19 dBSPL			



CE
0459



Sonova AG · Laubisrütistrasse 28
CH-8712 Stäfa · Switzerland

A Sonova brand

PHONAK
life is on

Phonak Virto™ 1

Phonak Virto I-R (I90/I70/I50/I30)


Technical Data

SP Receiver


2 cm³ coupler data

ANSI / ASA S3.22-2014 (R2020)
IEC 60118-0:2022

Output sound pressure level



Acoustic gain




Frequency range	<100 Hz – 7000 Hz			
Total harmonic distortion	500 Hz	800 Hz	1600 Hz	3200 Hz
	1.0%	1.0%	1.0%	1.0%
Expected operating time*	24 h			
Equivalent input noise level	19 dBSPL			

UP Receiver


2 cm³ coupler data

ANSI / ASA S3.22-2014 (R2020)
IEC 60118-0:2022

Output sound pressure level



Acoustic gain



Frequency range	<100 Hz – 5200 Hz			
Total harmonic distortion	500 Hz	800 Hz	1600 Hz	3200 Hz
	1.0%	1.0%	1.0%	1.0%
Expected operating time*	24 h			
Equivalent input noise level	19 dBSPL			

* Expected operating time of the rechargeable battery depends on active features, the use of wireless accessories, hearing loss, battery age and sound environment.



CE
0459



Sonova AG · Laubisrütistrasse 28
CH-8712 Stäfa · Switzerland

A Sonova brand

PHONAK
life is on